

## Rocker switch, 3-gang, 10 AX 250 V~ with rockers Universal 1-way/2-way switch



| Specification                                                                                                    | Order No. | Packing unit | GBP/piece<br>without VAT | PS | EAN           |
|------------------------------------------------------------------------------------------------------------------|-----------|--------------|--------------------------|----|---------------|
|  cream white glossy            | 2832 01   | 1/10         | 32.87                    | 29 | 4010337832010 |
|  pure white glossy            | 2832 03   | 1/10         | 32.87                    | 29 | 4010337832034 |
|  anthracite                   | 2832 28   | 1/10         | 35.33                    | 29 | 4010337832287 |
|  colour aluminium (lacquered) | 2832 26   | 1/10         | 39.08                    | 29 | 4010337832263 |
|  black matt (lacquered)       | 2832 005  | 1/10         | 39.08                    | 11 | 4010337038528 |
|  grey matt (lacquered)        | 2832 015  | 1/10         | 39.08                    | 11 | 4010337087120 |
|  stainless steel (lacquered)  | 2832 600  | 1/10         | 42.56                    | 29 | 4010337022053 |

### Technical data

|                                                     |         |
|-----------------------------------------------------|---------|
| Installation depth:                                 | 25 mm   |
| Connection cross section<br>- for conductors up to: | 2.5 mm² |

## Notes

- For screw attachment only.

---