








**British Standard rocker switch (BS EN 60669-1) 20 AX 250 V~ with rocker and control light Circuit breaker, 2-pole**



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2834 01	1/10	42.23	29	4010337078814
 pure white glossy	2834 03	1/10	42.23	29	4010337078821
 anthracite	2834 28	1/10	42.69	29	4010337078845
 colour aluminium	2834 26	1/10	45.49	29	4010337078838
 black matt	2834 005	1/10	45.49	29	4010337038573
 grey matt	2834 015	1/10	45.49	29	4010337087137
 stainless steel	2834 600	1/10	51.95	29	4010337022305

**Technische Daten**

Installation depth:	24 mm
Connection cross section - for conductors up to:	2 x 4 mm <sup>2</sup> or 1 x 6 mm <sup>2</sup>

## Hinweise

- For screw attachment only.
  - BS EN 60669-1.
-