








British Standard rocker switch (BS EN 60669-1) 20 AX 250 V~ with rocker and control light Circuit breaker, 2-pole



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|------|--------------------|----|---------------|
|  cream white glossy | 2834 01 | 1/10 | 42.23 | 29 | 4010337078814 |
|  pure white glossy | 2834 03 | 1/10 | 42.23 | 29 | 4010337078821 |
|  anthracite | 2834 28 | 1/10 | 42.69 | 29 | 4010337078845 |
|  colour aluminium | 2834 26 | 1/10 | 45.49 | 29 | 4010337078838 |
|  black matt | 2834 005 | 1/10 | 45.49 | 29 | 4010337038573 |
|  grey matt | 2834 015 | 1/10 | 45.49 | 29 | 4010337087137 |
|  stainless steel | 2834 600 | 1/10 | 51.95 | 29 | 4010337022305 |

Technische Daten

| | |
|---|--|
| Installation depth: | 24 mm |
| Connection cross section - for conductors up to: | 2 x 4 mm ² or 1 x 6 mm ² |

Hinweise

- For screw attachment only.
 - BS EN 60669-1.
-