







**British Standard rocker switch (BS EN 60669-1) 20 AX 250 V~ with rocker Circuit breaker, 2-pole**



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2836 01	1/10	35.09	29	4010337078944
 pure white glossy	2836 03	1/10	35.09	29	4010337078951
 anthracite	2836 28	1/10	35.74	29	4010337078975
 colour aluminium	2836 26	1/10	38.58	29	4010337078968
 black matt	2836 005	1/10	38.58	29	4010337038566
 grey matt	2836 015	1/10	38.58	29	4010337087144
 stainless steel	2836 600	1/10	44.83	29	4010337021933

**Technische Daten**

Installation depth:	24 mm
Connection cross section - for conductors up to:	2 x 4 mm <sup>2</sup> or 1 x 6 mm <sup>2</sup>

## Hinweise

- For screw attachment only.
  - BS EN 60669-1.
-