








Socket outlet with protective contact EURO-US 16 A 250 V~



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2840 01	-	-	-	4010337840015
 pure white glossy	2840 03	1/10	13.90	29	4010337840039
 pure white matt	2840 27	-	-	-	4010337840275
 anthracite	2840 28	-	-	-	4010337840282
 colour aluminium	2840 26	-	-	-	4010337840268
black matt	2840 005	-	-	-	4010337037873
 grey matt	2840 015	-	-	-	4010337087151
 stainless steel (lacquered)	2840 600	-	-	-	4010337022213

Technische Daten

Installation depth: 20 mm