

Rocker button, 3-gang 10 A 250 V~ with rockers NO contact, 1-pole



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2844 01	1/10	34.58	29	4010337082033
 pure white glossy	2844 03	1/10	34.58	29	4010337082040
 anthracite	2844 28	1/10	37.08	29	4010337082064
 colour aluminium	2844 26	1/10	40.77	29	4010337082057
 black matt	2844 005	1/10	40.77	29	4010337037903
 grey matt	2844 015	1/10	40.77	29	4010337087182
 stainless steel (lacquered)	2844 600	1/10	44.27	29	4010337021957

Technische Daten

Installation depth:	25 mm
Connection cross section - for conductors up to:	2.5 mm²

Hinweise

- For screw attachment only.
