© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

UPS for emergency set



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 pure white glossy	2918 03	1/5	237.73	34	4010337011767

Features

- Uninterruptible power supply for the Gira emergency set.
- If the mains input voltage drops or fails, the connected load continues to be supplied by the rechargeable battery without interruption.
- If the mains input voltage increases or is restored, the rechargeable battery is disconnected from the load again.
- The signal contact (M) can be used to signal the operating statuses “UPS active” or “Rechargeable battery defective”.

Technical data

Input voltage:	DC 24 V
Output voltage in rechargeable battery operation:	22.8 V ± 10%
Rated load in rechargeable battery operation:	130 mA for 1 h
Maximum load	
- in rechargeable battery operation:	300 mA for 15 min
- in mains operation:	250 mA
Battery/rechargeable battery	
- Type:	UR18500F
- UN no.:	3480
Installation:	in device box in accordance with DIN 49073

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Notes

- For installations in accordance with DIN VDE 0834.
- DIN VDE 0834 states that components with a limited service life (rechargeable battery) must be replaced 1 x per year.
- Please observe the regulations on the disposal of used batteries.

Scope of supply

- Blank cover plate is included with delivery.
- Rechargeable battery included with delivery.
