


UPS for emergency set



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white glossy	2918 03	1/5	237.73	34	4010337011767

Merkmale

- Uninterruptible power supply for the Gira emergency set.
- If the mains input voltage drops or fails, the connected load continues to be supplied by the rechargeable battery without interruption.
- If the mains input voltage increases or is restored, the rechargeable battery is disconnected from the load and recharged in normal mains operation.
- The signal contact (M) can be used to signal the operating statuses "UPS active" or "Rechargeable battery defective".

Technische Daten

Input voltage:	DC 24 V
Output voltage in rechargeable battery operation:	22.8 V ± 10%
Rated load in rechargeable battery operation:	130 mA for 1 h
Maximum load	
- in rechargeable battery operation:	300 mA for 15 min
- in mains operation:	250 mA
Battery/rechargeable battery	
- Type:	UR18500F
- UN no.:	3480
Installation:	in device box in accordance with DIN 49073

Hinweise

- For installations in accordance with DIN VDE 0834.
 - DIN VDE 0834 states that components with a limited service life (rechargeable battery) must be replaced 1 x per year.
 - Please observe the regulations on the disposal of used batteries.
-

Lieferumfang

- Blank cover plate is included with delivery.
 - Rechargeable battery included with delivery.
-