



Rocker switch insert 10 AX 250 V~ intermediate switch



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 with mounting claws	3107 00	1/10/100	20.26	01	4010337039174
 without mounting claws	3817 00	1/10	20.26	01	4010337039181

Merkmale

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.

Technische Daten

Installation depth	
- 3107 00:	32 mm
- 3817 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm ²
Rated output	
- LEDi/CFLi:	100 W

Hinweise

- Can also be connected to be illuminated.
