
© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Rocker switch insert 10 AX 250 V~ 2-way switch, 2-gang



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 with mounting claws	3108 00	1/10	26.39	01	4010337038979
 without mounting claws	3818 00	1/10	26.39	01	4010337038757

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- LED lighting elements can be inserted from the front as standard.
- Can also be used with 1-gang rocker.

Technical data

Installation depth:	32 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm²
Rated output - LEDi/CFLi:	100 W

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.