

Rocker indicator switch 10 AX 250 V~ with mounting plate and orange LED lighting element 230 V~ Universal 1-way/2-way switch



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white	3116 13	1/10	31.34	13	4010337112471

Merkmale

- With LED lighting element.
- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic or would that then be polycarbonate.

Technische Daten

- Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²
- Rated output
- LEDi/CFLi: 100 W

Hinweise

- Can also be connected to be illuminated.

Lieferumfang

- All devices are delivered including mounting plate, cable and duct entries.
- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.