



Insert pushbutton switch 10 AX 250 V~universal off/2-way switch



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 with mounting claws	3126 00	1/10/100	13.19	01	4010337039020
 without mounting claws	3836 00	1/10	13.19	01	4010337038962

Merkmale

- Unlike rocker switches, the rockers in pushbutton switches always return to their original position after actuation.
- The resulting uniform rocker position gives the electrical installation an organised, premium appearance.
- The aesthetics are greatly enhanced, especially with multiple combinations, for example housing several switches in one frame.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technische Daten

Installation depth	
- 3126 00:	32 mm
- 3836 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm ²
Rated output	
- LEDi/CFLi:	100 W

Hinweise

- Can also be connected to be illuminated.
