© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Insert pushbutton switch 10 AX 250 V~ universal off/2-way switch



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 with mounting claws	3126 00	1/10/100	13.19	01	4010337039020
 without mounting claws	3836 00	1/10	13.19	01	4010337038962

Features

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- The resulting uniform rocker position gives the electrical installation an organised, premium appearance.
- The aesthetics are greatly enhanced, especially with multiple combinations, for example housing several switches in one frame.

Technical data

Installation depth
- 3126 00: 32 mm
- 3836 00: 23 mm

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Rated output
- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.