




## Insert pushbutton switch 10 AX 250 V~2-way switch, 2-gang



| Spezifikation  | Bestell-Nr. | VE   | GBP/Stück o. MWSt. | PS | EAN           |
|--|-------------|------|--------------------|----|---------------|
|  with mounting claws      | 3128 00     | 1/10 | 31.20              | 01 | 4010337039075 |
|  without mounting claws | 3838 00     | 1    | 31.20              | 01 | 4010337064411 |

### Merkmale

- Unlike rocker switches, the rockers in pushbutton switches always return to their original position after actuation.
- The resulting uniform rocker position gives the electrical installation an organised, premium appearance.
- The aesthetics are greatly enhanced, especially with multiple combinations, for example housing several switches in one frame.
- Can also be used with 1-gang rocker.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3,5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

### Technische Daten

|  |                     |
|--|---------------------|
| Installation depth:                        | 32 mm               |
| Connection cross section                   |                     |
| - For rigid and flexible conductors up to: | 2.5 mm <sup>2</sup> |
| Rated output                               |                     |
| - LEDi/CFLi:                               | 100 W               |