© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Rocker button 10 A 250 V~ with inscription space 1-pole NO contact with sep. signal contact



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 grey	3152 30	1/10	23.78	14	4010337124061

Features

- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic” or would that then be polycarbonate.

Technical data

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Notes

- Can also be connected to be illuminated.

Scope of supply

- The "light", "bell" and "door" symbols are included.