



## Rocker button insert 10 A 250 V~ series button



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 with mounting claws	3153 00	1/10	17.96	01	4010337121145
 without mounting claws	3823 00	1/10	17.96	01	4010337121169

### Merkmale

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

### Technische Daten

#### Installation depth

- 3153 00: 32 mm
- 3823 00: 24 mm

#### Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>