


Blind rocker switch insert 10 A 250 V~



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 with mounting claws	3159 00	1/10/100	26.93	01	4010337039211
 without mounting claws	3879 00	1/10	26.93	01	4010337064428

Features

- Quick mounting (3.5 turns per mounting claw).
- Voltage check possible from the front.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- With block to prevent both sides from being switched on.
- Locked both electrically and mechanically.

Technical data

Installation depth	
- 3159 00:	32 mm
- 3879 00:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm ²

Notes

- Suitable for use as an auxiliary unit for the blind controller insert with auxiliary input.
