










## SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) Screw terminals



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	4183 01	1/5	9.86	01	4010337093558
 pure white glossy	4183 03	1/10/100	9.86	01	4010337093572
 pure white matt	4183 27	1/10	9.86	01	4010337093596
 anthracite	4183 28	1/10	11.03	11	4010337093602
 colour aluminium	4183 26	1/5	15.27	11	4010337093589
 black matt	4183 005	1/10	15.27	11	4010337093541
 grey matt	4183 015	1/5	15.27	11	4010337093565
 stainless steel	4183 600	1	21.54	11	4010337093619
	0183 01	-	-	-	4010337183013



0183 03

-

-

-

4010337183037



0183 27

-

-

-

4010337183273



0183 28

-

-

-

4010337183280



0183 26

-

-

-

4010337183266



0183 005

-

-

-

4010337037675



0183 015

-

-

-

4010337077268



0183 600

-

-

-

4010337021896

## Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Earthed support ring.

## Technische Daten

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

## Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.

---