





SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) Screw terminals



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  pure white matt (lacquered) | 4183 72 | 1/5 | 15.47 | 11 | 4010337117766 |
|  anthracite (lacquered) | 4183 73 | 1/5 | 15.47 | 11 | 4010337117735 |
|  black matt (lacquered) | 4183 74 | 1/5 | 15.47 | 11 | 4010337117773 |
|  grey matt (lacquered) | 4183 76 | 1/5 | 15.47 | 11 | 4010337117742 |

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

| | |
|--|--|
| Installation depth: | 32 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |

Ambient temperature

- increased contact protection:

0°C to +45°C

Hinweise

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
 - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-