GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) Screw terminals



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 pure white matt (lacquered)	4183 72	1/5	15.47	11	4010337117766
 anthracite (lacquered)	4183 73	1/5	15.47	11	4010337117735
 black matt (lacquered)	4183 74	1/5	15.47	11	4010337117773
 grey matt (lacquered)	4183 76	1/5	15.47	11	4010337117742

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm² to 2.5 mm²

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Ambient temperature
- increased contact protection: 0°C to +45°C

Notes

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
