

## Danish socket outlet 16 A 250 V~ 107-2-D1, DK 1-1b with increased contact protection (Safety Plus) System 55



| Spezifikation                                                                                         | Bestell-Nr. | VE  | GBP/Stück o. MWSt. | PS | EAN           |
|-------------------------------------------------------------------------------------------------------|-------------|-----|--------------------|----|---------------|
|  cream white glossy  | 4422 01     | 1/5 | 20.63              | 01 | 4010337092308 |
|  pure white glossy | 4422 03     | 1/5 | 20.63              | 01 | 4010337092322 |
|  pure white matt   | 4422 27     | 1/5 | 20.63              | 01 | 4010337092346 |
|  anthracite        | 4422 28     | 1/5 | 21.83              | 11 | 4010337092353 |
|  colour aluminium  | 4422 26     | 1/5 | 26.22              | 11 | 4010337092339 |
|  black matt        | 4422 005    | 1/5 | 26.22              | 11 | 4010337092292 |
|  grey matt         | 4422 015    | 1/5 | 26.22              | 11 | 4010337092315 |

### Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

- Earthed support ring.

---

## Technische Daten

Installation depth: 29 mm

Connection cross section  
- for conductors from: 1.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>

---

## Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.

---