









## SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus) System 55



| Spezifikation   | Bestell-Nr. | VE       | GBP/Stück o. MWSt. | PS | EAN           |
|---|-------------|----------|--------------------|----|---------------|
|  cream white glossy  | 4453 01     | 1/10/100 | 9.86               | 01 | 4010337093718 |
|  pure white glossy | 4453 03     | 1/10/100 | 9.86               | 01 | 4010337093732 |
|  pure white matt   | 4453 27     | 1/10/100 | 9.86               | 01 | 4010337093763 |
|  anthracite        | 4453 28     | 1/10/100 | 11.03              | 11 | 4010337093770 |
|  colour aluminium  | 4453 26     | 1/10     | 15.27              | 11 | 4010337093756 |
|  black matt        | 4453 005    | 1/10/100 | 15.27              | 11 | 4010337093701 |
|  grey matt         | 4453 015    | 1/5      | 15.27              | 11 | 4010337093725 |
|  stainless steel   | 4453 600    | 1/5      | 22.80              | 11 | 4010337093787 |

## Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

---

## Technische Daten

|  |  |
|--|--|
| Installation depth:                                    | 32 mm                                      |
| Conductors:  | Rigid and flexible                         |
| Connection cross section<br>- for conductors from:     | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |
| Ambient temperature<br>- increased contact protection: | 0°C to +45°C                               |

---

## Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-