


SCHUKO socket outlet 16 A 250 V~ with inscription space and increased contact protection (Safety Plus) System 55



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSSt. | PS | EAN |
|---|-------------|----|---------------------|----|---------------|
|  pure white glossy | 4462 03 | - | - | - | 4010337093381 |

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

| | |
|--|--|
| Installation depth: | 29 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature - increased contact protection: | 0°C to +45°C |

Hinweise

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.

Lieferumfang

- Inscription label "EDV" is enclosed.
