









Socket outlet with earth pin 16 A 250 V~ and increased contact protection (Safety Plus) System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	4485 01	1/5	11.64	01	4010337095668
 pure white glossy	4485 03	1/10/100	11.64	01	4010337095682
 pure white matt	4485 27	1/10	11.64	01	4010337095712
 anthracite	4485 28	1/10	12.83	11	4010337095729
 colour aluminium	4485 26	1/10	17.01	11	4010337095705
 black matt	4485 005	1/10	17.01	11	4010337095651
 grey matt	4485 015	1/5	17.01	11	4010337095675
 stainless steel	4485 600	1/5	24.57	11	4010337095736

Merkmale

- With plug terminals.
 - The support ring is earthed in connection with the mounting claws and claw screws.
 - Quick mounting (approx. 3.5 turns per mounting claw).
 - Expanding claws in the housing.
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
 - Low installation depth.
 - Large, ergonomically shaped release levers.
 - Sturdy earth bar with solid earthing fingers.
 - Sturdy and corrosion-resistant steel support ring.
 - Shatter-proof thermoplastic base.
-

Technische Daten

Installation depth:	29 mm
Replaces fully compatible 0485 ...:	
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature	
- increased contact protection:	0°C to +45°C

Hinweise

- Approved in accordance with NF C 61-314:2017.
 - Approved in accordance with NBN C 61-112-1:2017.
 - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-