GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Socket outlet with earth pin 16 A 250 V~ and increased contact protection (Safety Plus) System 55



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 cream white glossy	4485 01	1/5	11.64	01	4010337095668
 pure white glossy	4485 03	1/10/100	11.64	01	4010337095682
 pure white matt	4485 27	1/10	11.64	01	4010337095712
 anthracite	4485 28	1/10	12.83	11	4010337095729
 colour aluminium (lacquered)	4485 26	1/10	17.01	11	4010337095705
 black matt (lacquered)	4485 005	1/10	17.01	11	4010337095651
 grey matt (lacquered)	4485 015	1/5	17.01	11	4010337095675
 stainless steel	4485 600	1/5	24.57	11	4010337095736

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Features

- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Replaces fully compatible 0485 ...:	
Connection cross section - for conductors from:	1.5 mm² to 2.5 mm²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- Approved in accordance with NF C 61-314:2017.
- Approved in accordance with NBN C 61-112-1:2017.
- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
