





Socket outlet with earth pin 16 A 250 V~ and increased contact protection (Safety Plus)



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white matt (lacquered)	4485 72	1/5	17.14	11	4010337117988
 anthracite (lacquered)	4485 73	1/5	17.14	11	4010337117957
 grey matt (lacquered)	4485 76	1/5	17.14	11	4010337117964
 black matt (lacquered)	4485 74	1/5	17.14	11	4010337117995

Merkmale

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technische Daten

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Hinweise

- Approved in accordance with NF C 61-314:2017.
 - Approved in accordance with NBN C 61-112-1:2017.
 - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-