

Socket outlet with earth pin 16 A 250 V~, hinged cover and protección ampliada contra contacto accidental (Safety Plus) System 55



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 cream white glossy	4488 01	1/10	19.17	01	4010337095804
 pure white glossy	4488 03	1/10	19.17	01	4010337095835
 pure white matt	4488 27	1/10	19.17	01	4010337095859
 anthracite	4488 28	1/10	20.36	11	4010337095866
 colour aluminium (lacquered)	4488 26	1/10	24.57	11	4010337095842
 black matt (lacquered)	4488 005	1/10	24.57	11	4010337095798
 grey matt (lacquered)	4488 015	1/10	24.57	11	4010337095811
 stainless steel	4488 600	1/5	32.12	11	4010337095873

Features

- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature	
- increased contact protection:	0°C to +45°C

Notes

- Approved in accordance with NF C 61-314:2017.
 - Approved in accordance with NBN C 61-112-1:2017.
 - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-