









Socket outlet with earth pin 16 A 250 V~, hinged cover and protección ampliada contra contacto accidental (Safety Plus) System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	4488 01	1/10	19.17	01	4010337095804
 pure white glossy	4488 03	1/10	19.17	01	4010337095835
 pure white matt	4488 27	1/10	19.17	01	4010337095859
 anthracite	4488 28	1/10	20.36	11	4010337095866
 colour aluminium	4488 26	1/10	24.57	11	4010337095842
 black matt	4488 005	1/10	24.57	11	4010337095798
 grey matt	4488 015	1/10	24.57	11	4010337095811
 stainless steel	4488 600	1/5	32.12	11	4010337095873

## Merkmale

- With plug terminals.
  - The support ring is earthed in connection with the mounting claws and claw screws.
  - Quick mounting (approx. 3.5 turns per mounting claw).
  - Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## Technische Daten

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

---

## Hinweise

- Approved in accordance with NF C 61-314:2017.
  - Approved in accordance with NBN C 61-112-1:2017.
  - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
-