


## Switching actuator, 2-gang 16 A with manual actuation for KNX



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
	5007 00	1	324.00	66	4010337132073

DRA switching actuators with integrated bus coupler. For switching independently controllable groups of loads. With manual switch for switching over the relay (On/Off) parallel or without KNX operation. Multi-phase connection. No additional power supply required.

### Merkmale

⋮

Switch outputs

⋮

- Input monitoring for cyclic updating of the switching object with safety position.

Logic functions

⋮

### Technische Daten

KNX medium: TP256

KNX current consumption:

:

Switching voltage:

Current carrying capacity of adjacent outputs:

## Connections

- KNX: Connection and junction terminal  
- Load:

Ambient temperature: -5 °C to +45 °C

## Switching current

- AC1 pursuant to DIN EN IEC 60947-4-1: 16 A  
- Fluorescent lamps:  
- Maximum switch-on current:

## Loads per output

- Light bulbs:  
- HV LED lamps:  
- Motors:

---

## Hinweise

- KNX Data Secure compatible.  
- Configuration and start-up of the device from ETS 5 version 5.7.7 or higher or ETS 6 version 6.3 or higher (recommended).

---

## Lieferumfang

- Switching actuator.  
- KNX connection terminal.  
- Secure Card.  
- Operating instructions.

---

## Abmessungen

Teilungseinheiten (TE): 6

---