


## Power supply DC 12 V 2 A



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 DRA	5319 00	1	68.75	42	4010337774037

### Merkmale

- Power supply DC 12 V for the eNet server, eNet wireless receiver module and external camera.

### Technische Daten

Rated voltage	
- Primary:	AC 100 to 240 V, 50/60 Hz
- Secondary:	DC 12 to 14 V
Rated current	
- Secondary:	2 A
Leakage current:	max. 250 µA
Ambient temperature:	-10 °C to +50 °C

### Abmessungen

Teilungseinheiten (TE):	2
-------------------------	---