© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Power supply DC 12 V 2 A



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 DRA	5319 00	1	68.75	42	4010337774037

Features

- Power supply DC 12 V for the eNet server, eNet wireless receiver module and external camera.

Technical data

Rated voltage	
- Primary:	AC 100 to 240 V, 50/60 Hz
- Secondary:	DC 12 to 14 V
Rated current	
- Secondary:	2 A
Leakage current:	max. 250 µA
Ambient temperature:	-10 °C to +50 °C

Dimensions

Modular width (MW):	2

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.