


eNet Radio remote control, 1-gang



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 anthracite	5350 10	1	58.66	42	4010337774075

Merkmale

- One button for one channel.
- Status LED.
- Battery-operated device.

Can be set with eNet server:

- Fully encrypted wireless transmission (AES CCM) from eNet Server software version 2.0.
- Operation locks.
- All-On or All-Off scenes and individual scenes can be configured.
- Configuration of scene button using eNet SMART HOME App (if-then rules) to trigger actions, scenes and timers.
- Device software update.

Technische Daten

Rated voltage:	DC 3 V
Battery	
- Type:	CR 2450N
- UN no.:	3091
- W x H x D:	40,5 x 55 x 15 mm

Hinweise

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.

Lieferumfang

- Batteries are included with delivery.
