© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

eNet Radio remote control, 2-gang



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 anthracite	5352 10	1	58.66	42	4010337774082

Features

- Two buttons belong to each channel.
- Each pair of buttons can be set as channel or scene function.
- Status LED.
- Battery-operated device.

Technical data

Rated voltage:	DC 3 V
Battery	
- Type:	CR 2450N
- UN no.:	3091
Dimensions	
- W x H x D:	40,5 x 55 x 15 mm

Notes

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.

Scope of supply

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

- Batteries are included with delivery.
