









## System 3000 operating top unit System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	5360 01	1/5	25.78	02	4010337027201
 pure white glossy	5360 03	1/5	25.78	02	4010337027218
 pure white matt	5360 27	1/5	25.78	02	4010337027232
 anthracite	5360 28	1/5	28.47	02	4010337027249
 colour aluminium	5360 26	1/5	32.72	02	4010337027225
 black matt	5360 005	1/5	32.72	02	4010337037453
 grey matt	5360 015	1/5	32.72	02	4010337087205
 stainless steel	5360 600	1/5	40.45	02	4010337027256

### Technische Daten

Ambient temperature: -20°C to +45°C