









System 3000 operating top unit, 2-gang System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	5362 01	1/5	39.48	02	4010337063841
 pure white glossy	5362 03	1/5	39.48	02	4010337063858
 pure white matt	5362 27	1/5	39.48	02	4010337063896
 anthracite	5362 28	1/5	42.17	02	4010337063902
 colour aluminium	5362 26	1/5	46.44	02	4010337063889
 black matt	5362 005	1/5	46.44	02	4010337063919
 grey matt	5362 015	1/5	46.44	02	4010337087229
 stainless steel	5362 600	1/5	54.15	02	4010337063926

Technische Daten

Ambient temperature: -20°C to +45°C