










## System 3000 touch top unit System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	5365 01	1/5	80.94	02	4010337096856
 pure white glossy	5365 03	1/5	80.94	02	4010337096863
 pure white matt	5365 27	1/5	80.94	02	4010337096887
 anthracite	5365 28	1/5	83.75	02	4010337096894
 colour aluminium	5365 26	1/5	87.97	02	4010337096870
 black matt	5365 005	1/5	87.97	02	4010337096917
 grey matt	5365 015	1/5	87.97	02	4010337107071
 stainless steel	5365 600	1/5	95.81	02	4010337096900

## **Merkmale**

- Operated by gently touching or swiping the operating surface.
  - Three brightness values can be stored, with System 3000 dimming insert.
  - The runtime and an individual intermediate position can be saved using the System 3000 blind controller insert.
  - Blocking function, with System 3000 blind control insert.
  - Status display using LED light bars to indicate the brightness or hanging position.
  - Permanent or temporary status display (status display goes out after 5 seconds if not touched).
  - Operation on System 3000 switching, dimming or blind insert and 3-wire auxiliary unit.
- 

## **Technische Daten**

Ambient temperature: -5°C to +45°C

---