GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

System 3000 touch top unit System 55



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
cream white glossy	5365 01	1/5	80.94	02	4010337096856
pure white glossy	5365 03	1/5	80.94	02	4010337096863
pure white matt	5365 27	1/5	80.94	02	4010337096887
anthracite	5365 28	1/5	83.75	02	4010337096894
colour aluminium (lacquered)	5365 26	1/5	87.97	02	4010337096870
black matt (lacquered)	5365 005	1/5	87.97	02	4010337096917
grey matt (lacquered)	5365 015	1/5	87.97	02	4010337107071
stainless steel	5365 600	1/5	95.81	02	4010337096900

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Features

- Operated by gently touching or swiping the operating surface.
- Three brightness values can be stored, with System 3000 dimming insert.
- The runtime and an individual intermediate position can be saved using the System 3000 blind controller insert.
- Blocking function, with System 3000 blind control insert.
- Status display using LED light bars to indicate the brightness or hanging position.
- Permanent or temporary status display (status display goes out after 5 seconds if not touched).
- Operation on System 3000 switching, dimming or blind insert and 3-wire auxiliary unit.

Technical data

Ambient temperature:	-5°C to +45°C
