






## System 3000 touch top unit System 70



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSSt.	PS	EAN
 pure white glossy	5365 70	1/5	83.66	02	4010337124252
 pure white matt (lacquered)	5365 72	1/5	90.68	02	4010337124269
 anthracite (lacquered)	5365 73	1/5	90.68	02	4010337124276
 black matt (lacquered)	5365 74	1/5	90.68	02	4010337124283
 grey matt (lacquered)	5365 76	1/5	90.68	02	4010337124290

### Merkmale

- Operated by gently touching or swiping the operating surface.
- Three brightness values can be stored, with System 3000 dimming insert.
- The runtime and an individual intermediate position can be saved using the System 3000 blind controller insert.
- Blocking function, with System 3000 blind control insert.
- Status display using LED light bars to indicate the brightness or hanging position.
- Permanent or temporary status display (status display goes out after 5 seconds if not touched).
- Operation on System 3000 switching, dimming or blind insert and 3-wire auxiliary unit.

### Technische Daten

Ambient temperature: -5°C to +45°C