

System 3000 blind timer and timer Display System 55



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 cream white glossy	5366 01	1/5	94.07	02	4010337027430
 pure white glossy	5366 03	1/5	94.07	02	4010337027447
 pure white matt	5366 27	1/5	94.07	02	4010337027461
 anthracite	5366 28	1/5	96.80	02	4010337027478
 colour aluminium (lacquered)	5366 26	1/5	101.03	02	4010337027454
 black matt (lacquered)	5366 005	1/5	101.03	02	4010337037484
 grey matt (lacquered)	5366 015	1/5	101.03	02	4010337087243
 stainless steel (lacquered)	5366 600	1/5	108.77	02	4010337027485

Features

- Operation via capacitive sensor surface.
- Fast programming for adopting the current time as the programmed movement time/switching time.
- Automatic summer/winter time switchover, deactivatable.
- Switching at sunrise or sunset (astro function) adjustable for 18 countries.
- Astro time for sunrise and sunset can be individually adjusted by ± 2 hours.
- The blocking function blocks operation of the auxiliary unit and deactivates automatic mode.
- The display turns off after 2 minutes, permanent display of time is possible.
- Programming one raising and one lowering time or two switch-on and switch-off times for weekdays (Mon-Fri) and for the weekend (Sat+Sun).

Technical data

Accuracy

- Per month: ± 10 s

Power reserve: approx. 4 h

Ambient temperature: -5°C to $+45^{\circ}\text{C}$
