






System 3000 blind timer and timer Display System 70



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 pure white glossy	5366 70	1/5	96.64	02	4010337118565
 pure white matt (lacquered)	5366 72	1/5	103.60	02	4010337118572
 anthracite (lacquered)	5366 73	1/5	103.60	02	4010337118541
 black matt (lacquered)	5366 74	1/5	103.60	02	4010337118589
 grey matt (lacquered)	5366 76	1/5	103.60	02	4010337118558

Merkmale

- Operation via capacitive sensor surface.
- Fast programming for adopting the current time as the programmed movement time/switching time.
- Automatic summer/winter time switchover, deactivatable.
- Switching at sunrise or sunset (astro function) adjustable for 18 countries.
- Astro time for sunrise and sunset can be individually adjusted by ± 2 hours.
- The blocking function blocks operation of the auxiliary unit and deactivates automatic mode.
- The display turns off after 2 minutes, permanent display of time is possible.
- Programming one raising and one lowering time or two switch-on and switch-off times for weekdays (Mon-Fri) and for the weekend (Sat+Sun).

Technische Daten

Accuracy
- Per month: ± 10 s

GIRA Parts list

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Power reserve: approx. 4 h

Ambient temperature: -5°C to +45°C
