






System 3000 blind timer and timer Display System 70



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  pure white glossy | 5366 70 | 1/5 | 96.64 | 02 | 4010337118565 |
|  pure white matt (lacquered) | 5366 72 | 1/5 | 103.60 | 02 | 4010337118572 |
|  anthracite (lacquered) | 5366 73 | 1/5 | 103.60 | 02 | 4010337118541 |
|  black matt (lacquered) | 5366 74 | 1/5 | 103.60 | 02 | 4010337118589 |
|  grey matt (lacquered) | 5366 76 | 1/5 | 103.60 | 02 | 4010337118558 |

Merkmale

- Operation via capacitive sensor surface.
- Fast programming for adopting the current time as the programmed movement time/switching time.
- Automatic summer/winter time switchover, deactivatable.
- Switching at sunrise or sunset (astro function) adjustable for 18 countries.
- Astro time for sunrise and sunset can be individually adjusted by ± 2 hours.
- The blocking function blocks operation of the auxiliary unit and deactivates automatic mode.
- The display turns off after 2 minutes, permanent display of time is possible.
- Programming one raising and one lowering time or two switch-on and switch-off times for weekdays (Mon-Fri) and for the weekend (Sat+Sun).

Technische Daten

- Accuracy
- Per month: ± 10 s

GIRA Parts list

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Power reserve: approx. 4 h

Ambient temperature: -5°C to +45°C
