© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

System 3000 motion detector top unit 2.20 m Standard System 70



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 pure white glossy	5375 70	1/5	73.68	02	4010337118466
 pure white matt (lacquered)	5375 72	1/5	80.64	02	4010337118473
 anthracite (lacquered)	5375 73	1/5	80.64	02	4010337118442
 black matt (lacquered)	5375 74	1/5	80.64	02	4010337118480
 grey matt (lacquered)	5375 76	1/5	80.64	02	4010337118459

Features

- Automatic switching of lighting, depending on the movement of heat and ambient brightness.
- Operation with System 3000 switching or dimming insert or 3-wire auxiliary insert.
- Expansion of the detection range in combination with the 3-wire auxiliary insert.
- Adjustable brightness threshold.
- Sensitivity adjustable in four steps.
- If a System 3000 auxiliary insert with operating top unit or mechanical button is connected to the main unit, the lighting can be switched on or dimmed for the duration of the delay time.

With System 3000 dimming insert

- Switch on with the last brightness set, or a saved switch-on brightness.
- The switch-on brightness can only be saved permanently via the System 3000 auxiliary insert with operating top unit.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Technical data

Angle of detection:	180°
Brightness value	
- adjustable:	approx. 5 to 500 lx
- fixed:	Day mode
Sensitivity:	25, 50, 75, 100 %
Protection class	
- System 55, System 70:	IP20
- TX_44:	IP44
Delay time:	approx. 2 min fixed
Mounting height up to 2.20 m	
- Range of detection forwards:	Max. 15 m
- Range to each side:	Max. 10 m
Mounting height up to 1.10 m	
- Range of detection forwards:	Max. 10 m
- Range to each side:	Max. 9 m
Ambient temperature:	-20 °C to +45 °C