© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

System 3000 motion detector top unit 2.20 m Komfort BT System 55



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 cream white glossy	5376 01	1	118.07	02	4010337050261
 pure white glossy	5376 03	1	118.07	02	4010337050537
 pure white matt	5376 27	1	118.07	02	4010337050612
 anthracite	5376 28	1	120.77	02	4010337050636
 colour aluminium (lacquered)	5376 26	1	125.04	02	4010337050575
 black matt (lacquered)	5376 005	1	125.04	02	4010337050650
 grey matt (lacquered)	5376 015	1	125.04	02	4010337087304
 stainless steel (lacquered)	5376 600	1	132.76	02	4010337050674

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Features

- Automatic switching of lighting, depending on the movement of heat and ambient brightness.
- Operation with System 3000 switching or dimming insert or 3-wire auxiliary insert.
- Expansion of the detection range in combination with the 3-wire auxiliary insert.
- If a System 3000 auxiliary insert with operating top unit or mechanical button is connected to the main unit, the lighting can be switched on or dimmed for the duration of the delay time.
- Device facilitates manual switchover between automatic, always-on and always-off.

With System 3000 switching insert

- Short-term operation.

With System 3000 dimming insert

- Switch on with the last brightness set, or a saved switch-on brightness.
- The switch-on brightness can only be saved permanently via the System 3000 auxiliary insert with operating top unit.
- Basic light function.
- Night light function.

Functions with the Gira System 3000 app

- Set the brightness threshold.
- Individually adjustable sensitivity of the two sensors (0, 25, 50, 75, 100 %).
- Set the delay time.
- Override functions: Automatic mode, permanently on/off, time-limited on/off for 0.5 to 5 hours.
- Presence simulation.
- Switch-off pre-warning.
- Day mode.
- Walking test.
- Time-switch function.
- Automatic signal mode (flashing).
- Manual signal mode (flashing).

Technical data

Angle of detection:	180°
Brightness value	
- adjustable:	approx. 5 to 500 lx
- fixed:	Day mode
Sensitivity:	0, 25, 50, 75, 100 %
Protection class	
- System 55, System 70:	IP20
- TX_44:	IP44
Delay time:	Approx. 10 s to 60 min
Mounting height up to 2.20 m	
- Range of detection forwards:	Max. 15 m
- Range to each side:	Max. 10 m
Mounting height up to 1.10 m	
- Range of detection forwards:	Max. 10 m
- Range to each side:	Max. 9 m
Transmission power:	max. 2.5 mW, class 2
Transmission range:	typically 10 m

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Ambient temperature:	-20 °C to +45 °C