









Rocker, 2-gang audio control System 55



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  cream white glossy | 5384 01 | 1/5 | 11.92 | 02 | 4010337122739 |
|  pure white glossy | 5384 03 | 1/5 | 11.92 | 02 | 4010337122746 |
|  pure white matt | 5384 27 | 1/5 | 11.92 | 02 | 4010337122753 |
|  anthracite | 5384 28 | 1/5 | 14.45 | 02 | 4010337122760 |
|  colour aluminium | 5384 26 | 1/5 | 16.22 | 02 | 4010337122777 |
|  black matt | 5384 005 | 1/5 | 16.22 | 02 | 4010337122784 |
|  grey matt | 5384 015 | 1/5 | 16.22 | 02 | 4010337122791 |
|  stainless steel | 5384 600 | 1/5 | 19.31 | 02 | 4010337122807 |

Merkmale

- Rocker switches to replace the original rockers with printed symbols.
 - Universally usable for either left or right rocker.
-

Hinweise

- Using a metal top unit and/or metal cover frames can lead to impairments to the range.
-