GIRA Data sheet

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

eNet wireless control unit DALI, 1-gang Mini



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
	5422 00	1/5	136.87	42	4010337774198

Features

- The eNet wireless control unit DALI enables switching and brightness adjustment of DALI lights.
- Joint operation of all connected DALI ballasts, broadcast.
- DALI power supply for a maximum of twelve devices.
- Parallel connection of up to six DALI wireless control units Mini to supply power to up to 72 devices.
- Switch-on and minimum brightness can be saved.
- Scene operation.
- Status feedback to eNet radio transmitter.
- Short-circuit and excess-temperature protection.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 2 W
Ambient temperature:	-25 °C to +70 °C
DALI rated voltage:	DC 16 V
Output current:	max. 24 mA
Connection cross section:	Max. 4 mm²
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m
Dimensions - W x H:	53 x 28 mm

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Notes

- Mounting in device box, surface-mounted housing or in installation adapter.
