


## eNet wireless control unit DALI, 1-gang Mini



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
	5422 00	1/5	136.87	42	4010337774198

### Merkmale

- The eNet wireless control unit DALI enables switching and brightness adjustment of DALI lights.
- Joint operation of all connected DALI ballasts, broadcast.
- DALI power supply for a maximum of twelve devices.
- Parallel connection of up to six DALI wireless control units Mini to supply power to up to 72 devices.
- Switch-on and minimum brightness can be saved.
- Scene operation.
- Status feedback to eNet radio transmitter.
- Short-circuit and excess-temperature protection.

Can be set with eNet server:

- Maximum brightness.
- Dimming speed.
- Delay time.
- Switch-on/off delay.
- Dimming ramp up/down.
- Switch-off pre-warning.
- Permanent-on, permanent-off.
- Hotel function.
- Light control.
- Repeater function.
- Localisation of the device.

### Technische Daten

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 2 W
Ambient temperature:	-25 °C to +70 °C
DALI rated voltage:	DC 16 V
Output current:	max. 24 mA

Connection cross section:	Max. 4 mm <sup>2</sup>
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m
Dimensions - W x H:	53 x 28 mm

---

## Hinweise

- Mounting in device box, surface-mounted housing or in installation adapter.

---