© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

System 106 surface-mounted housing 2-gang

Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
traffic white (laquered)	5502 902	1	133.68	20	4010337022909
anthracite	5502 910	1	133.68	20	4010337022916

Independent of the construction progress, the housings can already be installed in the building shell. Cables and modules can then be added when they are needed.Housings available in metal alloy laquered in traffic white (RAL 9016) or anthracite: all robust materials which ensure durability.

Features

- Very low installation height of just 28.4 mm.
- Vertical and horizontal installation (only for surface-mounted housings, 2-gang, 3-gang, 4-gang and 5-gang) enables optimal adaptation to the installation site.
- Suitable for use on façades with a thermal insulation composite system.

Notes

- Surface-mounted housing, 1-gang only for use with door station module and System 106 Keyless In components.

Scope of supply

- Flat ribbon cable, 10-pole and terminating resistors are included with delivery (exception: surface-mounted housing, 1-gang).

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.