© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

DVI (24+5) insert Gender changer



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 pure white glossy	5644 03	1/5	99.56	01	4010337460732
 black matt	5644 10	1/5	99.56	01	4010337460749

Technical data

Installation depth
- Gender changer: mind. 12 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:Kaiser electronic boxesFlush-mounted installation: Kaiser order no.:1068-02Cavity mounting: Kaiser order no.:9062-94Concrete installation: Kaiser order no.:1268-40