



DVI (24+5) insert Breakout cable



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSSt. | PS | EAN |
|---|-------------|----|---------------------|----|---------------|
|  pure white glossy | 5645 03 | 1 | 113.81 | 01 | 4010337460763 |
|  black matt | 5645 10 | 1 | 113.81 | 01 | 4010337460770 |

Technische Daten

| | |
|-------------------------------|-------------|
| Installation depth | |
| - Breakout cable: | mind. 58 mm |
| Length of the breakout cable: | 200 mm |

Hinweise

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes
Flush-mounted installation: Kaiser order no.: 1068-02
Cavity mounting: Kaiser order no.: 9062-94
Concrete installation: Kaiser order no.: 1268-40