© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

SAT F jack insert, 2-gang Gender changer



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 pure white glossy	5651 03	1/5	55.31	01	4010337461005
 black matt	5651 10	1/5	55.31	01	4010337461012

Technical data

Installation depth:	20 mm
Wave impedance:	75 Ω
For internal conductors:	Ø 0.6 to 1 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:Kaiser electronic boxesFlush-mounted installation: Kaiser order no.:1068-02Cavity mounting: Kaiser order no.:9062-94Concrete installation: Kaiser order no.:1268-40